

# 760241725

---

Fiber Optic Panel, 1U, unloaded, for holding up to 3 LGX/1000 modules, black



## Product Classification

<b>Regional Availability</b>	Asia   China
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	1000-style

## General Specifications

<b>Application</b>	Accepts three LGX/1000 footprint panels/cassettes
<b>Cable Exit Location</b>	Rear, left side   Rear, right side
<b>Color</b>	Black
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	Unloaded
<b>Module/Adapter Pack Slots, quantity</b>	3
<b>Modules Included, quantity</b>	0
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding
<b>Splice Trays Included, quantity</b>	0

## Dimensions

<b>Height</b>	43.7 mm   1.72 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	308.1 mm   12.13 in

## Material Specifications

# 760241725

---

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

