

760245328 | CM24-2x6-LS-A

G2 MPOptimate® Multimode OM4 Conversion Module, (2) MPO-24 pinned ports rear, (6) MPO-8 pinned front, Method A Pair Straight



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	MPOptimate®

General Specifications

Functionality	Breakout
Adapters, quantity, front	3
Adapters, quantity, rear	2
Color, front	Aqua
Color, rear	Aqua
Data Module Type	Fiber Conversion Module
Interface, front	MPO
Interface Feature, front	Standard
Interface, rear	MPO
Interface Feature, rear	Key up Pinned
Polarity	Method A Pairs, straight
Shuttered	No
Total Fibers, quantity	48
Total Ports, quantity, front	6

Dimensions

Height	26.42 mm 1.04 in
Width	96.52 mm 3.8 in

760245328 | CM24-2x6-LS-A

Depth 117.35 mm | 4.62 in

Optical Specifications

Fiber Mode Multimode
Fiber Type OM4, LazrSPEED® 550
Insertion Loss, maximum 0.4 dB

Environmental Specifications

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

