

# CY2615-000 | OCM1-SP41400L2



OCM1 LGX Style Fiber Optic Splitter Module, Planar, four 1x4 Splitter, singlemode, LC/APC, symmetrical split ratio

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Splitter module
<b>Product Series</b>	LGX   OCM1

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Access</b>	Front
<b>Application</b>	For use with LGX panels
<b>Circuits, quantity</b>	4
<b>Distribution Type</b>	1 x 4 splitter
<b>Interface, front</b>	LC/APC
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	129.54 mm   5.1 in
<b>Width</b>	58.42 mm   2.3 in
<b>Depth</b>	127 mm   5 in

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

**Packaging Type**                      Box | Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

