


FMT-MS27A7A2500B00



FMT MicroVAM Fiber Optic Splitter Module, two 1x2 splitters, singlemode, SC/APC, 75/25 split ratio

Product Classification

| | |
|------------------------------|-----------------|
| Regional Availability | North America |
| Portfolio | CommScope® |
| Product Type | Splitter module |
| Product Series | FMT |

General Specifications

| | |
|---------------------------|---|
| Device Type | Micro VAM |
| Functionality | Splitting |
| Access | Front |
| Application | For use with FMT panels For use with NGF frames |
| Circuits, quantity | 2 |
| Distribution Type | 1 x 2 splitter |
| Interface, front | SC/APC |
| Interface, Input | SC/APC |
| Interface, Output | SC/APC |
| Split Ratio | 75/25 |
| Splitter, quantity | 2 |

Dimensions

| | |
|---------------|--------------------|
| Height | 71.88 mm 2.83 in |
| Width | 17.27 mm 0.68 in |
| Depth | 177.8 mm 7 in |

FMT-MS27A7A2500B00

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

