

# 760082503 | RK6-52A



Equipment Rack, 2-Post, 6 in (152 mm) Channel x 8 ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	2 post rack

## General Specifications

<b>Color</b>	Black
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	52
<b>Rail Mounting Hole</b>	#12-24

## Dimensions

<b>Height</b>	2,438.4 mm   96 in
<b>Channel Width</b>	152.4 mm   6 in
<b>Width</b>	518.16 mm   20.4 in
<b>Depth</b>	457.2 mm   18 in
<b>Dimensional Standards</b>	EIA-310-E

## Material Specifications

<b>Finish</b>	Powder-coated, textured
<b>Material Type</b>	Aluminum

## Mechanical Specifications

<b>Load Rating</b>	453.592 kg   1000 lb
<b>Load Rating Note</b>	per UL2416 standard

## Packaging and Weights

<b>Included</b>	Forty #12-24 x 1/2 in mounting screws   Instruction sheet   Twelve 3/8 in split lock
-----------------	--

# 760082503 | RK6-52A

---

washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Flat packed
<b>Weight, net</b>	16.33 kg   36.001 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

