



Equipment Rack, 4-Post, 29 in (737 mm) D x 7ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) 12-24 Tapped Rails, Black

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type 4 post rack

General Specifications

Color Black

Rack Type EIA 19 in

Rack Units 45

Rail Mounting Hole #12-24

Dimensions

Height 2,133.6 mm | 84 in

Channel Width 76.2 mm | 3 in

Width 518.16 mm | 20.4 in

Depth 1,041.4 mm | 41 in

Dimensional Standards EIA-310-E

Material Specifications

Finish Powder-coated, textured

Material Type Aluminum

Mechanical Specifications

Static Load Rating 907.2 kg | 2,000.031 lb

Environmental Specifications

Safety Standard UL | cUL

Packaging and Weights

Included Base pan | Forty #12-24 x 1/2 in mounting screws | Four vertical rack rails | Instruction sheet | Twenty four 3/8 in split lock washers | Twenty four 3/8-16 UNC x 1 in hex head bolts | Twenty four 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Upper plate support

Packaging quantity 1

Packaging Type Flat packed

Weight, net 35.83 kg | 78.992 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

