

# 760082560 | RK4P45-36A



Equipment Rack, 4-Post, 36 in (914 mm) D x 7 ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) 12-24 Tapped Rails, Black

## Product Classification

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio** CommScope®

**Product Type** 4 post rack

## General Specifications

**Color** Black

**Rack Type** EIA 19 in

**Rack Units** 45

**Rail Mounting Hole** #12-24

## Dimensions

**Height** 2,133.6 mm | 84 in

**Channel Width** 76.2 mm | 3 in

**Width** 518.16 mm | 20.4 in

**Depth** 1,219.2 mm | 48 in

**Dimensional Standards** EIA-310-E

## Material Specifications

**Finish** Powder-coated, textured

**Material Type** Aluminum

## Mechanical Specifications

**Static Load Rating** 907.2 kg | 2,000.031 lb

# 760082560 | RK4P45-36A

---

## Environmental Specifications

**Safety Standard** UL | cUL

## Packaging and Weights

**Included** Base pan | Forty #12-24 x 1/2 in mounting screws | Four vertical rack rails | Instruction sheet | Twenty four 3/8 in split lock washers | Twenty four 3/8-16 UNC x 1 in hex head bolts | Twenty four 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Upper plate support

**Packaging quantity** 1

**Packaging Type** Flat packed

**Weight, net** 44 kg | 97.003 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

