# 760221739 | PNL-CS-12LCX-PT



Product Classification

### OM4 Splicing cassette, 12LC , 900#m

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Brand	LazrSPEED®
General Specifications	
Adapter Color	Aqua
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	12
Total Ports, quantity, front	6
Dimensions	
Height	28.956 mm   1.14 in
Width	104.648 mm   4.12 in
Depth	165.354 mm   6.51 in
Pigtail Length	1.5 m   4.921 ft
Optical Specifications	
Fiber Mode	Multimode
Fiber Type	OM4, LazrSPEED® 550
Insertion Loss, typical	0.3 dB
Return Loss, minimum	25 dB

## **Environmental Specifications**

Safety Standard

UL

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

**COMMSCOPE**°

# 760221739 | PNL-CS-12LCX-PT

1

## Packaging and Weights

#### Packaging quantity

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

