

# CK3606-000 | FIST-GPS2-M-AJE5E-6

---

FIST-GPS2 Fiber Termination/Splice Panel, LSH/PC, 3RU, with 6 trays, ETSI width, gray

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Brand</b>	FIST®
<b>Product Series</b>	FIST-GPS2

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Application</b>	Used in FIST-GR3-style frames only
<b>Color</b>	Gray
<b>Color, front</b>	Gray
<b>Interface, front</b>	Unloaded
<b>Rack Type</b>	ETSI 600 mm
<b>Rack Units</b>	3
<b>Shelf Movement</b>	Sliding

## Dimensions

<b>Height</b>	133.35 mm   5.25 in
<b>Width</b>	531 mm   20.906 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Galvanized steel

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +45 °C (+23 °F to +113 °F)
<b>Storage Temperature</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Relative Humidity</b>	Up to 93%, non-condensing

## Packaging and Weights

# CK3606-000 | FIST-GPS2-M-AJE5E-6

---

<b>Included</b>	Mounting hardware
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

