


# CK4385-000 | FIST-GPS3-J-1

---



FIST-GPS3 Fiber Panel for holding up to 4 GPST Patch/Splice Trays, unloaded, 2RU, 15 in, gray

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Brand</b>	FIST®
<b>Product Series</b>	FIST-GPS3

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Application</b>	Used in FIST-GR3F-style frames only
<b>Color</b>	Gray
<b>Color, front</b>	Gray
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	Unloaded
<b>Rack Type</b>	EIA 15 in
<b>Rack Units</b>	2
<b>Shelf Movement</b>	Sliding

## Dimensions

<b>Height</b>	88 mm   3.465 in
<b>Width</b>	481 mm   18.937 in
<b>Depth</b>	280 mm   11.024 in

## Material Specifications

<b>Finish</b>	Powder coated
---------------	---------------

# CK4385-000 | FIST-GPS3-J-1

---

**Material Type** Galvanized steel

## Environmental Specifications

**Operating Temperature** -5 °C to +45 °C (+23 °F to +113 °F)

**Storage Temperature** -30 °C to +60 °C (-22 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

