

# 760157800 | OVRHDRACK



3 in (76 mm) Channel x 9.4 in (239 mm) H - 19 in (482.6 mm) Overhead Patch Panel Rack (4U) 3/8 Sq Punch, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Mini-rack, overhead

## General Specifications

<b>Color</b>	Black
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	4

## Dimensions

<b>Height</b>	238.76 mm   9.4 in
<b>Channel Width</b>	76.2 mm   3 in
<b>Width</b>	500.38 mm   19.7 in
<b>Depth</b>	76.2 mm   3 in
<b>Dimensional Standards</b>	EIA-310-E

## Material Specifications

<b>Finish</b>	Powder-coated, textured
<b>Material Type</b>	Steel

## Mechanical Specifications

<b>Static Load Rating</b>	27.2 kg   59.966 lb
---------------------------	---------------------

## Packaging and Weights

<b>Included</b>	Instruction sheet   Six 5/16-18 hex nuts   Six 5/16-18 hex screws   Sixteen M6 cage nuts   Sixteen M6 mounting screws   Two flat washers   Two ladder clamp brackets   Two mounting brackets
-----------------	--

# 760157800 | OVRHDRACK

---

**Packaging quantity** 1  
**Packaging Type** Assembled

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

