## 760237942 | EHD-SP-24LC-SMR-AS-ULL



EHD ULL 24f LC UPC ribbon splice cassette Singlemode, includes 2, FST-ACC006 mass fusion splice sleeves

#### **Product Classification**

Portfolio SYSTIMAX®

**Product Type** Fiber cassette with ribbon pigtail

Product Brand SYSTIMAX ULL

Product Series EHD

### General Specifications

Adapters, quantity, front 24
Adapters, quantity, rear 0

Color, front Blue
Interface, front LC/UPC

Interface, rear Ribbon pigtail

**Polarity** Method A | Pairs, straight

Total Fibers, quantity 24

Total Ports, quantity, front 24

#### **Dimensions**

 Height
 12.446 mm | 0.49 in

 Width
 169.672 mm | 6.68 in

 Depth
 163.83 mm | 6.45 in

## Optical Specifications

Fiber Type G.657.A2

## **Environmental Specifications**



# 760237942 | EHD-SP-24LC-SMR-AS-ULL

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity

**Weight, net** 0.454 kg | 1 lb

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### Included Products

FST-ACC006 – Fiber Optic Protective Splice Sleeve, 12f mass fusion, 5

pack