



EHD ULL Singlemode Splice Cassette, 24LC with dust plugs and ribbon pigtails

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with ribbon pigtail
Product Brand	SYSTIMAX ULL
Product Series	EHD

General Specifications

Color, front	Blue
Interface, front	LC/UPC
Interface, rear	Ribbon pigtail
Polarity	Method B Enhanced
Shuttered	No
Total Fibers, quantity	24

Dimensions

Height	11.43 mm 0.45 in
Width	169.672 mm 6.68 in
Depth	163.83 mm 6.45 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.25 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
--------------------------------	---------------------------

760238932 | EHD-SP-24LC-SMR-B-ULL

Safety Standard CE | CSA | UL

Packaging and Weights

Included Mass Fusion Splice Protection Sleeves

Packaging quantity 1

Weight, net 0.181 kg | 0.4 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

FST-ACC006 – Fiber Optic Protective Splice Sleeve, 12f mass fusion, 5 pack