760239129 | EHD-FT-00-LC-00-00



EHD 24 port LC field term splice cassette

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®
Product Type Fiber cassette

Product Series EHD

General Specifications

Color, frontBlackInterface, frontLC/UPCInterface, rearNo pigtail

Total Fibers, quantity 24

Dimensions

 Height
 11.43 mm | 0.45 in

 Width
 169.672 mm | 6.68 in

 Depth
 163.83 mm | 6.45 in

Environmental Specifications

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.159 kg | 0.35 lb

Regulatory Compliance/Certifications



760239129 | EHD-FT-00-LC-00-00

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

