

CK9479-000 | FIST-OSKG



FIST Gel Sealing Kit for oval splice closure port, sealing 1 looped cable with diameter between 5 and 18 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

Product Classification

Regional Availability	EMEA
Product Type	Gel sealing kit
Product Series	FIST-GCO2

General Specifications

Application	For use with FIST-GCO2 Fiber closures
Cable Capacity, maximum	1
Color	Black

Dimensions

Single Cable Diameter, maximum	18 mm 0.709 in
Single Cable Diameter, minimum	5 mm 0.197 in

Packaging and Weights

Included	Cable termination brackets Dummy plugs Multi-out gel seal
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

