FL2-48RPNL



FL2000 Fiber Termination Panel, unloaded, 48 Ports, 3RU, 19 in, putty white

Product Classification

| Regional Availability | Latin America North America |
|-----------------------|-------------------------------|
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |
| Product Series | FL2000 |
| | |

General Specifications

| Functionality | Patching |
|----------------------------|-------------|
| Color | Putty white |
| Growth Configuration | Unloaded |
| Interface, front | Unloaded |
| Rack Type | EIA 19 in |
| Rack Units | 3 |
| Shelf Movement | Hinged |
| Splicing Capacity, maximum | 0 |
| Total Ports, quantity | 48 |
| | |

Dimensions

| Height | 133.35 mm 5.25 in |
|--------|---------------------|
| Width | 482.6 mm 19 in |
| Depth | 256.54 mm 10.1 in |

Material Specifications

| Finish | Powder coated |
|---------------|---------------|
| Material Type | Steel |

Environmental Specifications

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024



FL2-48RPNL

| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
|-----------------------|--------------------------------------|
| Storage Temperature | -40 °C to +85 °C (-40 °F to +185 °F) |
| Packaging and Weights | |
| Included | Mounting hardware |
| Packaging quantity | 1 |
| | |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant |
| | |



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

