

# FL2-C770072PW-6C00

---

FL2000 Fiber Termination/Splice Panel, pre-terminated with pigtailed, 72 SC/UPC, singlemode, 8RU, 19 in, putty white

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	FL2000

## General Specifications


<b>Functionality</b>	Patching   Splicing
<b>Adapter Packs Included, quantity</b>	12
<b>Cable Exit Location</b>	Rear, left side   Rear, right side
<b>Color</b>	Putty white
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	SC/UPC
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	8
<b>Shelf Movement</b>	Hinged
<b>Splicing Capacity, maximum</b>	72
<b>Total Ports, quantity</b>	72

## Dimensions

<b>Height</b>	355.6 mm   14 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	256.54 mm   10.1 in

## Ordering Tree

# FL2-C770072PW-6C00



## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Packaging quantity</b>	1

# FL2-C770072PW-6C00

---

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

### Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

Compliant

