FL2-CA70012PW-1C02



FL2000 Fiber Termination/Splice Panel, pre-terminated with pigtails, 12 SC/UPC, singlemode, 2RU, 19 in, black

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series FL2000

General Specifications

Functionality Patching | Splicing

Adapter Packs Included, quantity 2

 Cable Exit Location
 Rear, left side | Rear, right side

Color Black

Growth ConfigurationFully loadedInterface, frontSC/UPCRack TypeEIA 19 in

Rack Units 2

Shelf MovementHingedSplicing Capacity, maximum12Total Ports, quantity12

Dimensions

 Height
 88.9 mm | 3.5 in


 Width
 482.6 mm | 19 in

 Depth
 256.54 mm | 10.1 in

Ordering Tree



FL2-CA70012PW-1C02



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

COMMSCOPE®

FL2-CA70012PW-1C02

Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
| | |

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

