


FL2-CB60048JN-2A02



FL2000 Fiber Termination/Splice Panel, pre-terminated with pigtails, 48 LC/UPC, multimode, 3RU, 19 in, putty white

Product Classification

| | |
|------------------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch/splice panel |
| Product Series | FL2000 |

General Specifications

| | |
|---|------------------------------------|
| Functionality | Patching Splicing |
| Adapter Packs Included, quantity | 4 |
| Cable Exit Location | Rear, left side Rear, right side |
| Color | Putty white |
| Growth Configuration | Fully loaded |
| Interface, front | LC/UPC |
| Rack Type | EIA 19 in |
| Rack Units | 3 |
| Shelf Movement | Hinged |
| Splicing Capacity, maximum | 48 |
| Total Ports, quantity | 48 |

Dimensions

| | |
|---------------|---------------------|
| Height | 133.35 mm 5.25 in |
| Width | 482.6 mm 19 in |
| Depth | 256.54 mm 10.1 in |

Ordering Tree

FL2-CB60048JN-2A02



Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Optical Specifications

| | |
|-------------------|-----------|
| Fiber Mode | Multimode |
|-------------------|-----------|

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Storage Temperature | -40 °C to +85 °C (-40 °F to +185 °F) |

Packaging and Weights

| | |
|---------------------------|-------------------|
| Included | Mounting hardware |
| Packaging quantity | 1 |

FL2-CB60048JN-2A02

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

