

FL2-S4704A030-CD00



FL2000 Fiber Termination Panel, 48 SC/UPC, singlemode, 3RU, 19 in, putty white, pre-terminated with IFC cable, 30 meters, Stub tail at far end

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with IFC cable
Product Series	FL2000

General Specifications


Functionality	Patching
Adapter Packs Included, quantity	8
Cable Exit Location	Downward
Cable Stub Type	IFC
Color	Putty white
Color, front	Putty white
Growth Configuration	Fully loaded
Interface, front	SC/UPC
Interface, rear	Stub tail
Patching Capacity, maximum	48
Rack Type	EIA 19 in
Rack Units	3
Shelf Movement	Hinged
Splicing Capacity, maximum	0
Total Ports, quantity	48

Dimensions

Height	133.35 mm 5.25 in
Width	482.6 mm 19 in
Depth	256.54 mm 10.1 in
Cable Length	30 m 98.425 ft

FL2-S4704A030-CD00

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

FL2-S4704A030-CD00

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

