

# FL2-SB80YA027-AU00

---



FL2000 Fiber Termination Panel, 48 LC/UPC, singlemode, 2RU, 19 in, putty white, pre-terminated with IFC cable, 27 meters, Stub tail at far end

## Product Classification

|                              |                                   |
|------------------------------|-----------------------------------|
| <b>Regional Availability</b> | Latin America   North America     |
| <b>Portfolio</b>             | CommScope®                        |
| <b>Product Type</b>          | Fiber patch panel, with IFC cable |
| <b>Product Series</b>        | FL2000                            |

## General Specifications

|   |              |
|---|--------------|
| <b>Functionality</b>                    | Patching     |
| <b>Adapter Packs Included, quantity</b> | 4            |
| <b>Cable Exit Location</b>              | Upward       |
| <b>Cable Stub Type</b>                  | IFC          |
| <b>Color</b>                            | Putty white  |
| <b>Growth Configuration</b>             | Fully loaded |
| <b>Interface, front</b>                 | LC/UPC       |
| <b>Interface, rear</b>                  | Stub tail    |
| <b>Rack Type</b>                        | EIA 19 in    |
| <b>Rack Units</b>                       | 2            |
| <b>Shelf Movement</b>                   | Hinged       |
| <b>Splicing Capacity, maximum</b>       | 0            |
| <b>Total Ports, quantity</b>            | 48           |

## Dimensions

|                     |                     |
|---------------------|---------------------|
| <b>Height</b>       | 88.9 mm   3.5 in    |
| <b>Width</b>        | 482.6 mm   19 in    |
| <b>Depth</b>        | 256.54 mm   10.1 in |
| <b>Cable Length</b> | 27 m   88.583 ft    |

# FL2-SB80YA027-AU00

## Ordering Tree



## Material Specifications

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Storage Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

# FL2-SB80YA027-AU00

---

**Packaging quantity**

1

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

