

FPS-FMTSP-AJJ01

FMT Fiber Optic Splitter Patch Panel, 1U, 19 in, 1x32 splitter, SC/APC splitter and output connect., 1 splitter



Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Splitter patch panel
Product Series	FMT

General Specifications

Device Type	Patch panel
Functionality	Splitting
Access	Front
Circuits, quantity	1
Distribution Type	1 x 32 splitter
Interface, front	SC/UPC
Rack Units	1
Split Ratio	Symmetrical
Splitter, quantity	1
Total Ports, quantity	33

Dimensions

Height	71.88 mm 2.83 in
Width	17.27 mm 0.68 in
Depth	177.8 mm 7 in

Optical Specifications

Directivity, minimum	60 dB
-----------------------------	-------

FPS-FMTSP-AJJ01

Polarization Dependent Loss, maximum	0.3 dB
Uniformity, maximum	1.5 dB
Wavelength Range	1260–1635 nm
Insertion Loss, Splitter, maximum	16.7 dB
Insertion Loss, Splitter, typical	16.5 dB
Return Loss, Splitter, minimum	55 dB

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
------------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

