

C100-BNFMR

CNT-100 CNT® Jumper with interface types N Female Bulkhead and MCX Male Right Angle, variable length



Product Classification

| | |
|-----------------------|------------------------|
| Product Type | Braided cable assembly |
| Product Brand | CNT® |
| Product Series | CNT-100 |

General Specifications

| | |
|---|---|
| Body Style, Connector A | Bulkhead |
| Body Style, Connector B | Right angle |
| Cable Family | CNT-100 |
| Interface, Connector A | N Female |
| Interface, Connector B | MCX Male |
| Orientation | 0° |
| Specification Sheet Revision Level | A |
| Variable Length | For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative |

Dimensions

| | |
|---------------------|------------|
| Length | 0 m 0 ft |
| Nominal Size | 0.100 in |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 700–3000 MHz | 1.433 | 14.99 |

Jumper Assembly Sample Label

C100-BNFMR



Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

- 100PMR-CR – MCX Male Right Angle for CNT-100 braided cable
- CNT-100-FR – CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket