

# C100-BNFMR

## Base Product

CNT-100 CNT® Jumper with interface types N Female Bulkhead and MCX Male Right Angle, variable length



## Product Classification

|                |                        |
|----------------|------------------------|
| Product Type   | Braided cable assembly |
| Product Brand  | CNT®                   |
| Product Series | CNT-100                |

## General Specifications

|                                    |   |
|------------------------------------|---|
| Body Style, Connector A            | Bulkhead  |
| Body Style, Connector B            | Right angle   |
| Cable Family                       | CNT-100   |
| Interface, Connector A             | N Female  |
| Interface, Connector B             | MCX Male  |
| Orientation                        | 0°  |
| Specification Sheet Revision Level | A   |
| Variable Length                    | For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative |

## Dimensions

|              |            |
|--------------|------------|
| Length       | 0 m   0 ft |
| Nominal Size | 0.100 in   |

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 700–3000 MHz   | 1.433 | 14.99            |

## Jumper Assembly Sample Label

# C100-BNFMR



## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



## Included Products

|            |  |
|------------|--|
| 100PMR-CR  | - MCX Male Right Angle for CNT-100 braided cable   |
| CNT-100-FR | - CNT-100-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket |