

C240-NMNR

Base Product



CNT-240 CNT® Jumper with interface types N Male and N Male Right Angle, variable length

Product Classification

| | |
|-----------------------|------------------------|
| Product Type | Braided cable assembly |
| Product Brand | CNT® |
| Product Series | CNT-240 |

General Specifications

| | |
|---|---|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Right angle |
| Cable Family | CNT-240 |
| Interface, Connector A | N Male |
| Interface, Connector B | N Male |
| Specification Sheet Revision Level | A |
| Variable Length | For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative |

Dimensions

| | |
|---------------------|------------|
| Length | 0 m 0 ft |
| Nominal Size | 0.240 in |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 700–3000 MHz | 1.288 | 18 |

Jumper Assembly Sample Label

C240-NMNR



Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

- 240BPNM-C-CR – Type N Male for CNT-240 braided cable
- CNT-240 – CNT-240, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket