

F1-PBMBM

FSJ1-50A Jumper with interface types BNC Male and BNC Male, variable length



Product Classification

Product Type SureFlex® standard

Product Series FSJ1-50A

General Specifications

Attachment, Connector A Field attachment

Attachment, Connector B Field attachment

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A BNC Male

Interface, Connector B BNC Male

Specification Sheet Revision Level A

Variable Length For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Length 0 m | 0 ft

Nominal Size 1/4 in

Electrical Specifications

DTF, Connector A -23 dB

DTF, Connector B -23 dB

Jumper Assembly Sample Label

F1-PBMBM



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

