

# F1A-PDMDM

---

FSJ1-50A SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, variable length



## Product Classification

|                       |                    |
|-----------------------|--------------------|
| <b>Product Type</b>   | SureFlex® standard |
| <b>Product Series</b> | FSJ1-50A           |

## General Specifications

|   |               |
|---|---------------|
| <b>Body Style, Connector A</b>            | Straight      |
| <b>Body Style, Connector B</b>            | Straight      |
| <b>Interface, Connector A</b>             | 7-16 DIN Male |
| <b>Interface, Connector B</b>             | 7-16 DIN Male |
| <b>Specification Sheet Revision Level</b> | A             |

## Dimensions

|                     |            |
|---------------------|------------|
| <b>Length</b>       | 0 m   0 ft |
| <b>Nominal Size</b> | 1/4 in     |

## VSWR/Return Loss

| <b>Frequency Band</b> | <b>VSWR</b> | <b>Return Loss (dB)</b> |
|-----------------------|-------------|-------------------------|
| <b>700–3000 MHz</b>   | 1.288       | 18                      |

## Jumper Assembly Sample Label

# F1A-PDMDM



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

