

F1A-PNMDM

FSJ1-50A SureFlex® Jumper with interface types N Male and 7-16 DIN Male, variable length



Product Classification

| | |
|-----------------------|--------------------|
| Product Type | SureFlex® standard |
| Product Series | FSJ1-50A |

General Specifications

| | |
|---|---|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | N Male |
| Interface, Connector B | 7-16 DIN Male |
| Specification Sheet Revision Level | A |
| Variable Length | For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative |

Dimensions

| | |
|---------------------|------------|
| Length | 0 m 0 ft |
| Nominal Size | 1/4 in |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 700–3000 MHz | 1.43 | 15.04 |

Jumper Assembly Sample Label

F1A-PNMDM



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

