


AJXMPMXCG

Base Product



Ultra Low Loss ULL LazrSPEED® 550 MPO(Unpinned) to MPO(Pinned)
Pre-terminated Trunk Cable, MPO12, 36-Fiber, LSZH, 12 fiber PmP 2.0
mm Dca, Method A

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle
East/Africa | North America

Portfolio

CommScope®

Product Type

Fiber trunk cable assembly

Ordering Note

For additional jacket colors, please contact a CommScope Sales
Representative | For lengths greater than 999 ft (304 m), orders must be
in meters | Minimum length may vary based on cable configuration

General Specifications

Color, boot A

Black

Color, connector A

Black

Color, boot B

Black

Color, connector B

Black

Construction Type

Stranded

Furcation Color

Aqua

Interface, Connector A

MPO-12/UPC Female

Interface, Connector B

MPO-12/UPC Male

Jacket Color

Aqua

Polarity

Method A

Fibers per Subunit, quantity

12

Total Fibers, quantity

36

Dimensions

Breakout Length


33 in

AJXMPMXCG

Cable Assembly Length Range (m) 3 – 999

Cable Assembly Length Range (ft) 10 – 999

Ordering Tree



Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

EN50575 CPR Cable EuroClass Fire Performance Dca

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ANATEL | Compliant |
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |



Included Products

- 760227231 N-036-MP-5K-F12AQ/20T/D – Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 36 fiber multi-unit with 12 fiber 2.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color, Dca flame rating
- 860659006 – MPO12, ULL, MALE, OM3/4, AQUA, 2MM
- 860659012 – MPO12, ULL, FEMALE, OM3/4, AQUA, 2MM