## AQGMPMPGD

#### **Base Product**



Singlemode MPO12 (Unpinned) to MPO12 (Unpinned), Fiber Patch Cord, 12-Fiber, Method A, Plenum

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

**Product Type** Fiber array cable assembly

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

#### General Specifications

 Color, boot A
 Black

 Color, connector A
 Green

 Color, boot B
 Black

 Color, connector B
 Green

 Construction Type
 Stranded

 Furcation Color
 Yellow

 Interface, Connector A
 MPO-12/APC Female

 Interface, Connector B
 MPO-12/APC Female

Jacket ColorYellowPolarityMethod A

Fibers per Subunit, quantity 12

Total Fibers, quantity 12

#### **Dimensions**

Cable Assembly Length Range (m) 1 - 305


Cable Assembly Length Range (ft) 1 - 999

Page 1 of 3



## AQGMPMPGD

#### Ordering Tree



#### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

**Fiber Mode** Singlemode

**Fiber Type** G.652.D | G.657.A2, TeraSPEED®

### **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



#### Included Products

760074955 – Fiber indoor cable, TeraSPEED® Plenum for MPO Light Duty Patchcords, 12 fiber, Singlemode

Page 2 of 3

# AQGMPMPGD

P-012-MP-8W-F30YL

860638318

G.652.D and G.657.A1, Feet jacket marking, Yellow jacket color MPO12, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm