# AQX2X2XHF

#### **Base Product**



OM4 MPO24 (Pinned) to MPO24 (Pinned), Fiber Patch Cord, 24-Fiber, Method A, Plenum

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

**Product Type** Fiber array cable assembly

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

### General Specifications

Color, boot ARedColor, connector AAquaColor, boot BRedColor, connector BAquaConstruction TypeStranded

Interface, Connector A MPO-24/UPC Male

Interface, Connector B MPO-24/UPC Male

Aqua

Jacket Color Aqua

**Polarity** Method A

Fibers per Subunit, quantity 24

Total Fibers, quantity 24

#### Dimensions

**Furcation Color** 


Cable Assembly Length Range (m) 1 - 305

Cable Assembly Length Range (ft) 1 - 999

### Ordering Tree



# X2X2XHF



## Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0° | 4.40 lb @ 90°

**Optical Specifications** 

**Fiber Mode** Multimode

**Fiber Type** OM4, LazrSPEED®

## **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Indoor | Plenum

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



860489152

### Included Products

Fiber indoor cable, LazrSPEED® Plenum MPO Light Duty for Patchcords, 24 fiber, Multimode 760161901 P-024-MP-5K-F36AQ OM4, Feet jacket marking, Aqua jacket color

LazrSPEED® Elite MPO Male 24 Fiber Connector, aqua

**COMMSCOPE®**