## DFJ-2M5A-HW

HELIAX® Discrete, 2 multimode fiber, 5 mm LSZH cable. End 1: DLC. End
2: DLC

#### Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

**Product Type** Wireless Fiber Cable Assemblies

Product Brand HELIAX®
Product Series DFJ

Ordering Note CommScope® non-standard product

General Specifications

**Construction Type** Discrete fiber tail

Interface, Connector A DLC

Interface Body Style, connector A Straight

Interface, Connector B DLC

Interface Body Style, connector B Straight

Jacket Color Black

Total Fibers, quantity 2

Dimensions


Cable Assembly Length Range (m) 1 - 200

**Diameter Over Jacket** 5 mm | 0.197 in

Ordering Tree



# DFJ-2M5A-HW



### Material Specifications

Jacket Material Low Smoke Zero Halogen (LSZH)

Optical Specifications

**Fiber Type** OM2, bend insensitive

**Insertion Loss, typical note** Insertion loss is measured at 850 nm

Insertion Loss, typical 0.5

#### **Environmental Specifications**

Operating Temperature -20 °C to +70 °C (-4 °F to +158 °F)

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

**Cable weight** 35 kg/km | 23.519 lb/kft

#### Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



### \* Footnotes

**Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)

