

C100-BNFSR-2M

CNT-100 CNT® Jumper with interface types N Bulkhead Female and SMA Male Right Angle, 2 m



Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-100

General Specifications

Body Style, Connector A	Bulkhead
Body Style, Connector B	Right angle
Cable Family	CNT-100
Interface, Connector A	N Female
Interface, Connector B	SMA Male
Specification Sheet Revision Level	A

Dimensions

Length	2 m 6.562 ft
Nominal Size	0.100 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.329	17

Jumper Assembly Sample Label

C100-BNFSR-2M



Included Products

- CNT-100-FR – CNT-100-FR, CNT[®] 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket