

# F1A-QMQM-20

---

FSJ1-50A SureFlex® Jumper with interface types QMA Male and QMA Male, 20 ft



## Product Classification

|                       |                                      |
|-----------------------|--------------------------------------|
| <b>Product Type</b>   | Wireless transmission cable assembly |
| <b>Product Brand</b>  | HELIAX®   SureFlex®                  |
| <b>Product Series</b> | FSJ1-50A                             |

## General Specifications

|   |          |
|---|----------|
| <b>Body Style, Connector A</b>            | Straight |
| <b>Body Style, Connector B</b>            | Straight |
| <b>Interface, Connector A</b>             | QMA Male |
| <b>Interface, Connector B</b>             | QMA Male |
| <b>Specification Sheet Revision Level</b> | A        |

## Dimensions

|                     |                 |
|---------------------|-----------------|
| <b>Length</b>       | 6.096 m   20 ft |
| <b>Nominal Size</b> | 1/4 in          |

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 700–3000 MHz   | 1.288 | 18               |

## Jumper Assembly Sample Label

# F1A-QMQM-20

---



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |