

F1P43A-PNMNM-10M

FSJ1P-50A SureFlex® Jumper with interface types N Male and N Male,
10 m



Product Classification

| | |
|-----------------------|---------------------|
| Product Type | SureFlex® standard |
| Product Brand | HELIAX® SureFlex® |
| Product Series | FSJ1-50A |

General Specifications

| | |
|---|----------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | N Male |
| Interface, Connector B | N Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|------------------|
| Length | 10 m 32.808 ft |
| Nominal Size | 1/4 in |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 695–806 MHz | 1.15 | 23.13 |
| 806–960 MHz | 1.13 | 24.29 |
| 1427–1535 MHz | 1.13 | 24.29 |
| 1700–2300 MHz | 1.15 | 23.13 |
| 2535–2655 MHz | 1.25 | 19.08 |
| 3400–3800 MHz | 1.25 | 19.08 |

Jumper Assembly Sample Label

F1P43A-PNMNM-10M



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |