

F4-HMHM-1M5-SGW-D



D-CLASS HELIAX® 1/2" Superflexible SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male with HELIAX® SureGuard weatherproofing, 1.5m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

| | |
|-----------------------|--------------------------------|
| Product Type | SureFlex® D-CLASS, dynamic PIM |
| Product Brand | HELIAX® SureFlex® |
| Product Series | RSJ4-50 |

General Specifications

| | |
|---|-------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | 4.3-10 Male |
| Interface, Connector B | 4.3-10 Male |
| Specification Sheet Revision Level | B |

Dimensions

| | |
|---------------------|------------------|
| Length | 1.5 m 4.921 ft |
| Nominal Size | 1/2 in |

Logo Image

F4-HMHM-1M5-SGW-D



Electrical Specifications

| | |
|--|------------------------------------|
| 3rd Order IMD Dynamic | -119 dBm |
| 3rd Order IMD Dynamic Test Method | Two +43 dBm carriers per IEC 62037 |
| DTF, Connector A | -34 dB |
| DTF, Connector B | -34 dB |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|-----------------------|-------------|-------------------------|
| 698–960 MHz | 1.065 | 30.04 |
| 1700–2200 MHz | 1.065 | 30.04 |
| 2200–2700 MHz | 1.083 | 27.99 |
| 3400–3800 MHz | 1.222 | 20.01 |

Jumper Assembly Sample Label

F4-HMHM-1M5-SGW-D



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX® SureGuard weatherproofing boot

Packaging and Weights

Included Weatherproofing boot

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS | Compliant |
| UK-ROHS | Compliant |

