

F2A-HMHM-35-SGW



FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male with SureFlex® SureGuard weatherproofing, 35 ft

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	Wireless transmission cable assembly
Product Series	FSJ2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	10.668 m 35 ft
Nominal Size	3/8 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.23	20

Jumper Assembly Sample Label

F2A-HMHM-35-SGW



Environmental Specifications

- Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition
- Weatherproofing Method** HELIAX® SureGuard weatherproofing boot