

F4S-HPHMDR-M5-SGW



RSJ4-50 SureFlex® Jumper with interface types 4.3-10 Male and 7-16 Right Angle DIN Male with HELIAX® SureGuard weatherproofing, 0.5 meter

- If there are threads along the entire device port length, the HELIAX® SureGuard weatherproofing solutions will only seal properly if the HSG-M29-ADPT adapter is installed on the device port

Product Classification

| | |
|-----------------------|-------------------------------|
| Product Type | SureFlex® Premium, static PIM |
| Product Brand | HELIAX® SureFlex® |
| Product Series | RSJ4-50 |

General Specifications

| | |
|---|---------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Right angle |
| Interface, Connector A | 4.3-10 Male |
| Interface, Connector B | 7-16 DIN Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|-----------------|
| Length | 0.5 m 1.64 ft |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|---|----------------------|
| 3rd Order IMD Static | -119 dBm |
| 3rd Order IMD Static Test Method | Two +43 dBm carriers |
| DTF, Connector A | -34 dB |
| DTF, Connector B | -34 dB |

VSWR/Return Loss

| Frequency Band | VSWR, typical | Return Loss, typical (dB) |
|----------------|---------------|---------------------------|
| 698–960 MHz | 1.083 | 27.99 |
| 1700–2200 MHz | 1.083 | 27.99 |
| 2200–2700 MHz | 1.135 | 23.98 |

F4S-HPHMDR-M5-SGW

Jumper Assembly Sample Label



Environmental Specifications

| | |
|-------------------------------|---|
| Immersion Test Method | Meets IEC 60529:2001, IP68 in mated condition |
| Weatherproofing Method | HELIAX® SureGuard weatherproofing boot |

Packaging and Weights

| | |
|-----------------|----------------------|
| Included | Weatherproofing boot |
|-----------------|----------------------|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

Included Products

| | |
|---------|---|
| RSJ4-50 | – RSJ4-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket |
|---------|---|