

# F2-HMNM-20-SGW1-D

---



D-CLASS FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male and N Male with HELIAX® SureGuard weatherproofing boot on one HM side 1 m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

<b>Product Type</b>	SureFlex® D-CLASS, dynamic PIM
<b>Product Series</b>	FSJ2-50

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	4.3-10 Male
<b>Interface, Connector B</b>	N Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	6.096 m   20 ft
<b>Nominal Size</b>	3/8 in

## Electrical Specifications

<b>3rd Order IMD Dynamic</b>	-112 dBm
<b>3rd Order IMD Dynamic Test Method</b>	Two +43 dBm carriers per IEC 62037

## Logo Image

# F2-HMNM-20-SGW1-D



## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.11	26.4
1700-2200 MHz	1.11	26.4
2500-2700 MHz	1.11	26.4

## Jumper Assembly Sample Label

Batch    Manufacturing Date (two digit year and week)

Manufacturing Plant    Product Revision

0123456789    US22    1240    /A

COMMSCOPE Andrew Solutions™

**F4-DMDM-2M-D** — Part Number

2 M (6.562 FT)  
SUREFLEX ASSEMBLY  
U.S. PATENT 5802710

Product of UNITED STATES    12US220001242 — Serial Number



# F2-HMNM-20-SGW1-D

---

## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

**Weatherproofing Method** HELIAX® SureGuard weatherproofing boot

## Packaging and Weights

**Included** Weatherproofing boot

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

