

F2A-HRDM-M31-TMB

FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male Right angle 7-16 DIN Male , 0.31m



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	Wireless transmission cable assembly
Product Series	FSJ2-50

General Specifications

Body Style, Connector A	Right angle
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	A

Dimensions

Length	0.31 m 1.017 ft
Nominal Size	3/8 in

Electrical Specifications

3rd Order IMD	-117 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.1	26.45
1700–2200 MHz	1.1	26.45
2200–2700 MHz	1.1	26.45

Jumper Assembly Sample Label

F2A-HRDM-M31-TMB



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Included Products

- FSJ2-50 – FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket