

# L4-PNRDM-30-X

---

LDF4-50A Jumper with interface types N Male Right Angle and 7-16 DIN Male, 9.14 m



## Product Classification

<b>Product Type</b>	SureFlex® standard
<b>Product Series</b>	LDF4-50A

## General Specifications

<b>Attachment, Connector B</b>	Field attachment
<b>Body Style, Connector A</b>	Right angle
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	7-16 DIN Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	9.14 m   29.987 ft
<b>Nominal Size</b>	1/2 in

## Electrical Specifications

<b>DTF, Connector A</b>	-32 dB
-------------------------	--------

## Jumper Assembly Sample Label

# L4-PNRDM-30-X



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system



## Included Products

- |           |   |  |
|-----------|---|--|
| L4TDM-PS  | - | 7-16 DIN Male Positive Stop™ for 1/2 in LDF4-50A cable   |
| L4TDM-PSA | - | 7-16 DIN Male Positive Stop™ for 1/2 in AL4RPV-50, LDF4-50A, HL4RPV-50 cable   |
| L4TNR-HC  | - | Type N Male Right Angle for 1/2 in LDF4-50A cable  |
| LDF4-50A  | - | LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket (Halogen free jacketing non-fire-retardant) |