

L4RN-PNMNR-15M-CAS



LDF4RK-50A SureFlex® Jumper with interface types N Male and N Male Right Angle, 15M

Product Classification

| | |
|-----------------------|--------------------------------------|
| Product Type | Wireless transmission cable assembly |
| Product Brand | HELIAX® SureFlex® |
| Product Series | LDF4-50A |

General Specifications

| | |
|---|-------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Right angle |
| Interface, Connector A | N Male |
| Interface, Connector B | N Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|------------------|
| Length | 15 m 49.213 ft |
| Nominal Size | 1/2 in |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) | Insertion Loss (dB) |
|----------------|-------|------------------|---------------------|
| 700–2500 MHz | 1.222 | 20.01 | 2.129 |

Jumper Assembly Sample Label

L4RN-PNMNR-15M-CAS



Environmental Specifications

| | |
|--|---|
| EN50575 CPR Cable EuroClass Fire Performance | B2ca |
| EN50575 CPR Cable EuroClass Smoke Rating | s1a |
| EN50575 CPR Cable EuroClass Droplets Rating | d1 |
| EN50575 CPR Cable EuroClass Acidity Rating | a1 |
| Immersion Test Method | Meets IEC 60529:2001, IP68 in mated condition |