

F2A-PDMDM-1M5

FSJ2-50 SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 1.5 m



Product Classification

Product Type SureFlex® standard

Product Series FSJ2-50

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A 7-16 DIN Male

Interface, Connector B 7-16 DIN Male

Specification Sheet Revision Level A

Dimensions

Length 1.5 m | 4.921 ft

Nominal Size 3/8 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.23	20

Jumper Assembly Sample Label

F2A-PDMDM-1M5



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

- | | |
|----------|--------------------------------------------------------------------------------------------------------------|
| 35422-42 | - Heat Treated FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket |
| FSJ2-50 | - FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket |