

F4RS-HPHMHM-4



HELIAX® 1/2" Superflexible Fire retardant SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 4 feet Black non-halogenated, fire retardant polyolefin jacket

Product Classification

| | |
|-----------------------|-----------------------------------|
| Product Type | SureFlex® HP, HELIAX® performance |
| Product Brand | HELIAX® SureFlex® |
| Product Series | RSJ4-50 |

General Specifications

| | |
|---|-------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | 4.3-10 Male |
| Interface, Connector B | 4.3-10 Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|--------------------|
| Length | 1.219 m 3.999 ft |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|---|----------------------|
| 3rd Order IMD Static Test Method | Two +43 dBm carriers |
| 3rd Order IMD, typical | -119 dBm |
| DTF, Connector A | -34 dB |
| DTF, Connector B | -34 dB |

VSWR/Return Loss

| Frequency Band | VSWR, typical | Return Loss, typical (dB) |
|----------------|---------------|---------------------------|
| 680–960 MHz | 1.065 | 30.04 |
| 1700–2200 MHz | 1.065 | 30.04 |
| 2200–2700 MHz | 1.083 | 27.99 |
| 3400–3800 MHz | 1.222 | 20.01 |

F4RS-HPHMHM-4

Jumper Assembly Sample Label



Environmental Specifications

| | |
|---|---|
| EN50575 CPR Cable EuroClass Fire Performance | B2ca |
| EN50575 CPR Cable EuroClass Smoke Rating | s1a |
| EN50575 CPR Cable EuroClass Droplets Rating | d1 |
| EN50575 CPR Cable EuroClass Acidity Rating | a1 |
| Immersion Test Method | Meets IEC 60529:2001, IP68 in mated condition |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |