

# PTS1P-DMDF-1M-P

---

PTS1-50-P SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Female, 1M



## Product Classification

<b>Product Type</b>	SureFlex® Premium, static PIM
<b>Product Series</b>	PTS1-50-P

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	7-16 DIN Male
<b>Interface, Connector B</b>	7-16 DIN Female
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	1 m   3.281 ft
<b>Nominal Size</b>	1/4 in

## Electrical Specifications

<b>3rd Order IMD Static</b>	-110 dBm
<b>3rd Order IMD Static Test Method</b>	Two +43 dBm carriers

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.152	23.02
1700–2200 MHz	1.152	23.02
2200–2700 MHz	1.152	23.02

## Jumper Assembly Sample Label

# PTS1P-DMDF-1M-P



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

