



ION® Standard Interface Card for Active Intelligent Point of Interface

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Product Type	Point of interface card
Product Brand	ION®

General Specifications

Functionality	Module alarm status Rack summary alarm status Rack /Subrack address setting
General Alarm	Integrated into management system
Management Interface	Summary alarm output
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.

Dimensions

Height	172.9 mm 6.807 in
Width	35.3 mm 1.39 in
Depth	422 mm 16.614 in

Electrical Specifications

Input Voltage	12 Vdc
Electrical Safety Standard	EN 60950-1
Power Consumption	6 W

Environmental Specifications

Operating Temperature	+5 °C to +50 °C (+41 °F to +122 °F)
Storage Temperature	-25 °C to +70 °C (-13 °F to +158 °F)
Relative Humidity	46%–94%
Mean Time Between Failures (MTBF) at Temperature	6,170,000 h @ 25 °C

Packaging and Weights

Height, packed	335 mm 13.189 in
Width, packed	172 mm 6.772 in
Depth, packed	625 mm 24.606 in
Weight, gross	1 kg 2.205 lb
Weight, net	0.5 kg 1.102 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

