


552041-1



PICABOND® Connector, 1000 strip, mini, blue

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for high count straight splicing applications

OBSOLETE

This product was discontinued on: June 1, 2016

Replaced By:

552041-3	PICABOND® Connector, 1000 strip, mini, blue
BR0299-000	PICABOND® Connector, 1000 strip, mini, blue

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Product Type	Splice
Product Brand	PICABOND®
Product Series	PICABOND

General Specifications

Connector Color Code	Blue
Connector Sealant	Unfilled
Connector Splicing Type	Bridge Butt Full bridge Half-tap Straight (In-line)

Dimensions

Compatible Conductor Gauge, solid	26–22 AWG
--	-----------

Electrical Specifications

Safety Voltage Rating	48 Vdc
------------------------------	--------

Material Specifications

Contact Base Material	Brass
Contact Plating Material	Tin

552041-1

Insulation Material

Air Core PIC | Paper or Pulp

Environmental Specifications

Operating Temperature

-40 °C to +60 °C (-40 °F to +140 °F)

Environmental Space

Outdoor

Packaging and Weights

Packaging quantity

1000

Packaging Type

Strip

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

