



Vertical Cable Management Kit, 12in X 8.4in (305mm X 213.4mm) Double Sided, With Doors, Silver

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America
Portfolio CommScope®
Product Type Vertical cable management

General Specifications

Configuration Type Double-sided
Color Silver
Door, quantity 2

Dimensions

Height 2,133.6 mm | 84 in
Width 304.8 mm | 12 in
Depth 558.8 mm | 22 in

Trough Capacity

Ordered Installation - 40%						
VCM Width	Cat 5e		Cat 6		Cat 6A	
	Front Trough	Rear Trough	Front Trough	Rear Trough	Front Trough	Rear Trough
6 in	492	492	397	397	248	248
8 in	671	671	541	541	338	338
10 in	850	850	685	685	429	429
12 in	1029	1029	829	829	518	518
Randomized Installation - 20%						
VCM Width	Cat 5e		Cat 6		Cat 6A	
	Front Trough	Rear Trough	Front Trough	Rear Trough	Front Trough	Rear Trough
6 in	246	246	198	198	124	124
8 in	335	335	270	270	169	169
10 in	425	425	343	343	214	214
12 in	514	514	415	415	259	259

Top View of VCM

Example for 8" VCM Capacity (Randomized Installation - 20%)

Material Specifications

Finish Powder-coated, smooth

Material Type Metal

Environmental Specifications

Safety Standard UL | cUL

Packaging and Weights

Included Four 1/2-20 hex nuts | Four 1/2-20 x 1 in hex head bolts | Four flat washers | Instruction sheet | Two spools

Packaging quantity 1

Packaging Type Assembled

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

