

OG3LX6-L-CS1-HC



HELIAX®, LC Loopback, Multimode

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Fiber loopback
Product Brand	HELIAX®

General Specifications

Interface	LC/UPC
------------------	--------

Mechanical Specifications

Mating Durability, maximum	0.5 dB @ 500 cycles
-----------------------------------	---------------------

Optical Specifications

Insertion Loss, maximum	1 dB
--------------------------------	------

Environmental Specifications

Operating Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
------------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

