

VIP6102W | VIP6102W UHD IP Set-Top

Base Product



IP, HEVC, Ultra-HD Set-Top with 802.11ac Wi-Fi

- UHD 4k x 2k p60 10-bit
- HDR (HDR10, HLG & Dolby Vision)
- Android TV certified, supports RDK 3.0, ARRIS KreaTV
- MediaKind MediaFirst®, TiVo®, MobiTV and Minerva integrated
- Multiple video codecs – including HEVC, MPEG-4 AVC (H.264), MPEG-2, VP9 and VC-1
- Supports network DVR/PVR with an internal SD Card Slot for a Pause Live TV buffer
- Universal Remote Control friendly, supports IR and Bluetooth® Low Energy options

The VIP6102W provides a stunning ultra high definition 4K video viewing experience. This stylish compact UHD IP client offers whole-home DVR/PVR and time-shift capabilities when using appropriate middleware.

The set-top offers a choice of software platforms; it is Android TV™ certified, and is RDK 3.0 and ARRIS KreaTV capable, along with many 3rd party Middleware, opening up a wide-range of User Interface options. 802.11ac Wi-Fi connectivity ensures high quality IPTV delivery without network cables.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	IP video device

General Specifications

Memory	16 GB eMMC 2 GB LP-DDR4
Network Interface	Ethernet Wi-Fi
Processor	Quad-core, 15000 DMIPS
Remote Interfaces	Bluetooth Low Energy (optional) IR
Software Compatibility	ARRIS KreaTV Android TV RDK 3.0
Tuner	IP
Video Formats	UHD
Video Resolution	1080i 1080p60 2160p60 10-bit 480i 480p 4Kp60 576i 576p 720p
Wi-Fi Interface Standard	4x4 IEEE 802.11ac @ 5 GHz

Dimensions

Height	155.956 mm 6.14 in
Width	136.906 mm 5.39 in
Length	20.828 mm 0.82 in

VIP6102W | VIP6102W UHD IP Set-Top

Logo Image



Electrical Specifications

Power Consumption 24 W

Environmental Specifications

Relative Humidity 8%–95%

Standards Compliance CE | FCC Certified | RoHS Compliant | UL Certified | VA/VIA June-2013 Agreement | WEEE

Packaging and Weights

Weight, net 0.34 kg | 0.75 lb